# Heraeus



# **Heraeus Noblelight** Light Hammer 6 MARK II

### Superior Technology and Unparalleled Service

Heraeus Noblelight is known for its superior UV curing technology and service capabilities. We invented microwave-powered UV curing technology over thirty-five years ago and today produce the most advanced UV curing systems available. Couple that with Heraeus Noblelight's unparalleled service capabilities and you'll understand why manufacturers, large and small, trust Heraeus Noblelight for their UV curing needs.

## **Continual Innovation and Improvement**

- Simplicity and flexibility in the control scheme
  - Software versus hardware
- Ease of integration, high compatibility
- Backward compatible with existing LH6 installations
- Increased uptime and reliability of product
  - Minimization of unscheduled downtime
- Multiple communication protocols
  - DeviceNet<sup>™</sup>, Profibus<sup>®</sup>, EtherNet/IP<sup>™</sup>, Dry Contact, and "Plug & Play" options
- Power Factor Correction
  - Eliminate electrical harmonics, better than 99% at full load
- Reduced weight and better air flow
  - For more efficient cooling

### Specifications: Light Hammer 6 MARK II

#### System Designations & Requirements

Available Input Voltages (50/60 Hz): 200 V-480 V ±10% auto-ranging.

System Ambient Operating Temperature:  $0-50^{\circ}C$ . System Ambient Storage Temperature:  $-40^{\circ}C-70^{\circ}C$ .

Power Supply: LHP6 MARK II.

Altitude: 0-1,000 m.

Irradiator: I6 series.

**Relative Humidity:** 30–95% (non-condensing). **Mobility:** Stationary rack-mounted operation.

Environmental: Indoor use only.

**Pollution Degree:** 2. **Compliance:** TÜV; CE.

#### Test Standards

Electrical Safety: EN 61010-1.

Emissions (CE): EN 55011 (CISPR-11) for Class A Group 2 device. Immunity (CE): EN 61000-6-4; EN 61000-6-2; EN 61000-4-x.

#### Irradiator Models: I6P Series, I6S Series, I6 with Modular Blower (I6B)

Operating Voltage: Powered through the LHP6 MARK II power supply.

**Exhaust:** Recommend 130% of the nominal volume of cooling air be exhausted.

**Reflector Geometry:** Semi-elliptical (with bulb at focus). **Mounting Position:** Any angle with respect to vertical. **Footprint:** 168 mm (6.6 in.) x 168 mm (6.6 in.).

Substrate Location: 53 mm (2.1 in.) from face of lamp, for maximum

Magnetron Output @ 100% Power: 184 W/cm (467 W/in.).

Bulb Fills: D, H, V.

**Cooling:** Cooling recommended at 100% operation (rapid cycling mode and reduced cooling excluded).


- I6P Series and I6S Series: 3.7 m<sup>3</sup>/min. (132 scfm)
   Test point pressure: 0.9 kPa (3.7 in. H<sub>2</sub>0).
- I6B and I6B MARK II: Integral.

#### **HVAC** Requirement Filtered:\*

- I6P Series (I6P1, I6P1LH): 1.4 kPa (5.5 in. H<sub>2</sub>O) (top air inlet)
   (I6P3, I6P3LH): 1.3 kPa (5.0 in. H<sub>2</sub>O) (side air inlet).
- I6S Series (I6S, I6SLH, I6SULC): 1.3 kPa (5.0 in. H<sub>2</sub>0) (side inlet)
   I6B and I6B MARK II: Integral.

#### NOTES:

\*All I6 irradiator measurements assume 100% power and 100% duty cycle. If operating at different power levels or under rapid cycling conditions, please contact **Heraeus Noblelight** for the cooling air requirements.



- I6P1, I6P1LH: 9.7 kg (21.4 lbs.) (top air inlet).
- I6P3, I6P3LH: 9.1 kg (20.0 lbs.) (side air inlet).
- I6S, I6SLH: 10.8 kg (23.9 lbs.) (stainless steel housing).
- I6SULC: 10.8 kg (23.9 lbs.) (stainless steel housing).
- I6B: 13.1 kg (28.8 lbs.).
- I6B MARK II: 13.1 kg (28.8 lbs.).

#### **I6B MARK II Blower Specifications**

Weight: Part of lamp unit: 13.1 kg (28.8 lbs.).

**Maximum Dimensions (W x D x H):** Irradiator/blower: 168 mm x 168 mm x 757 mm (6.6 in. x 6.6 in. x 29.8 in.).

**Operating Voltage:** Powered through the LHP6B MARK II power supply. **Ambient Conditions:** 45°C max. inlet temperature. 95% max. relative humidity, non-condensing.

**Altitude:** 0–1.000 m.

 $\label{eq:performance: 16B MARK II blower delivers a minimum pressure of 1,750 (7.0 inches to the I6B MARK II irradiator test port. (Use non-swept reflectors only.).}$ 

Noise: 76 dBA @ 1 m.

Specifications subject to change without notice.

**NOTE:** The LHP6B MARK II should be used in lightshields with unrestricted air flow. When a quartz plate assembly is used below the irradiator, a negative pressure exhaust system is required that eliminates back pressure at the base of the irradiator.

#### LH6 MARK II - Power Supply Power Level Control Options Method **Percent Control Modes of Operation** DeviceNet™, Profibus®, EtherNet/IP™ 1% steps Remote/DeviceNet™, Profibus®, EtherNet/IP™ (additional module required) 4-20 mA input 1% steps, via master/slave operation Remote/dry contact master/slave 0-10 V input 1% steps, via master/slave operation Remote/dry contact master/slave 4-bit binary input Remote/dry contact master/slave 5% steps, via master/slave operation Front panel switched 1% steps, via master/slave operation Local/front panel Specifications subject to change without notice.

#### Legacy K6 Blower Specifications

**NOTE:** The K6 Blower is for Legacy systems. The LHP6B MARK II power supply is backward compatible with a legacy I6B Lamp system containing the K6 Blower.

**Electrical:** Powered through I6B irradiator. **Mechanical:** Integral to I6B irradiator.

Noise: 78.5 dBA @ 1 m.

**Filter:** A replaceable polyester filter prefilters the cooling air entering the blower. Filters must be non-woven, bonded polyester fiber with a maximum continuous operating temperature of 250°F. The bonding agent must be flame and fungus retardant as well as moisture proof. The air velocity is 200–450 fpm.

Replacement filters are available from Heraeus Noblelight.

Specifications subject to change without notice.

**NOTE:** The I6B should be used in lightshields with unrestricted air flow. When a quartz plate assembly is used below the irradiator, a negative pressure exhaust system is required that eliminates back pressure at the base of the irradiator.

### LHP6 MARK II Power Supply

Weight: 18 kg (39 lbs.) (no blower control module) 20 kg (44 lbs.) with blower control module.

**Dimensions (W x H x L):** 419 mm x 217 mm x 777 mm with connector (16.5 in.  $\times$  8.5 in.  $\times$  30.6 in. with connector).

**Cooling Air Flow:** Air flow path: front to rear. **Input Voltages:** 200 V–480 V (auto-ranging).

Mounting Position: Horizontal unit can be free standing, stacked, or rack

mounted.

Line Power @ 100%: 5 kVA.

Clearance: Allow 305 mm (12 in.) clearance front and rear of the power supply

for cooling air flow and cable connections.

Safety Interlocks: E-stop. External interlock (customer I/O). RF fault.

Mag. Current @ 100% Power: 840 mA/magnetron.

Mag. Current Output Accuracy:  $\pm 1\%$ .

**Output Range:** 35% to 100%.

3-Phase: 50/60 Hz.

**Max. Line Current:** At 380-480 V: 7.25-5.8 (8.8-7.2 A with blower module installed). At 200-240 V: 13.3-11.1 A (17.1-14.0 A with blower module

installed).

**Stacking:** 5 units maximum. **Enclosure Rating:** IP20 (NEMA 1).

**Front Panel Indicators/Controls:** Lamp enable switch. USB port. OLED display unit with on/standby/off buttons and power level control buttons.

Rear Panel Connectors: J101: AC power input. J102: Master/slave.

J103: HV control. J104: Irradiator control. J105: RF detector. J106: Customer I/O. J107: E-stop. J108: Optional blower. J109/J110: Master/slave bus (option for LH6 legacy only).

J111: Optional comm bus. **Ventilation:** Internal fans.

**Filter:** Polyurethane foam, 30 pores per inch (PPI). **Audible Noise Level:** 65 dBA @ 1 m (at lamp off/reset).

Specifications subject to change without notice.

Contact your local Heraeus Noblelight office for an engineered solution for your specific requirements.

### Global reach, local presence.

Heraeus Noblelight also has experienced distributors around the world, most with factory trained service technicians.



#### heraeus-noblelight.com/fusionuv

Germany

#### Heraeus Noblelight GmbH

Heraeusstraße 12-14 63450, Hanau Phone +49 6181 35 4499 Fax +49 6181 35 9926 hng-uv@heraeus.com USA

#### Heraeus Noblelight America LLC

910 Clopper Road Gaithersburg, Maryland 20878-1357, USA Phone +1 301 527 2660 Fax +1 301 527 2661 info.hna.uvp@heraeus.com Japan

#### Heraeus K.K.

Noblelight Division Sumitomo Fudosan Otowa Building 1F, 2F, 5F 2-9-3 Otsuka, Bunkyo-ku 112-0012, Tokyo Phone +81 3 6902 6602 Fax +81 3 6902 6613

info.hkk@heraeus.com

China

#### Heraeus Noblelight (Shenyang) Ltd.

ISO 9001 Certified QMS

Shanghai Branch 2F, 5th Building 5 No. 406, Guilin Rd, Xuhui District Shanghai 200233, P.R. China Phone +86 21 5445 2255

+86 21 5445 2410

info.hns@heraeus.com

We reserve the right to incorporate changes and improvements without notice. HNG UVP57 EN/02.16/Cueto\_Reed